

SPECIFICATION SHEET

• N6D MULTISHELF MEDIUM TEMP DAIRY/DELI WEDGE MERCHANDISER •

Refrigeration Data:

			CAPACITY	(BTUH / CASE)			DISCHARG	AVG. REF.	
MODEL	CASE LENGTH	CASE USAGE	PARALLEL	CONVENTIONAL	EVAPORATOR (°F)	UNIT SIZING (°F)	TEMPERATURE (°F)	VELOCITY (FPM)	CHARGE (LBS/CASE)
N6DL30OS	39-5/8"	MED TEMP	5,133	5,500	+21	+19	+34	210	N/A
N6DL45IS	43-7/8"	MED TEMP	4,353	4,664	+21	+19	+32	400	N/A
N6DL45OS	51-1/16"	MED TEMP	5,257	5,633	+21	+19	+34	210	N/A
N6DL90IS	70-7/8"	MED TEMP	4,353	6,664	+21	+19	+32	396	N/A
N6DM45OS	51-1/16"	MED TEMP	5,441	5,830	+21	+19	+34	210	N/A
N6DM90IS	70-7/8"	MED TEMP	4,199	4,499	+21	+19	+32	396	N/A
N6DM90OSNL	78-7/8"	MED TEMP	7,909	8,474	+21	+19	+34	209	N/A
N6DH45IS	43-7/8"	MED TEMP	4,658	8,771	+21	+19	+32	400	N/A
N6DH45OS	51-1/16"	MED TEMP	5,625	6,027	+21	+19	+32	210	N/A
N6DH90IS	70-7/8"	MED TEMP	4,049	4,338	+21	+19	+32	396	N/A

^{*} Capacity data listed for cases with 1 row of T-8 canopy lights, optional T-8 shelf lighting. For sizing all refrigeration equipment other than TYLER, use conventional BTUH values.

FOR SPECIFIC COMPRESSOR SIZING INFORMATION, REFER TO TYLER APPLICATIONS FOR RACK SYSTEM COMPRESSORS AND/OR THE COMPRESSOR MANUFACTURERS FOR SINGLE COMPRESSORS. FOR LINE SIZING INFORMATION, REFER TO THE MISCELLANEOUS SECTION "BUFF" IN THE TYLER SPECIFICATION GUIDE.

Electrical Data:

Fans and Heaters (120 Volt)

	CASE	TOTAL FANS / STANDARD FANS			OTAL 1 FANS	TOTAL ANTI-SWEATS		
MODEL	LENGTH	CASE	AMPS	WATTS	AMPS	WATTS	AMPS	WATTS
N6DL30OS	39-5/8"	1	0.80	71.0	N/A	N/A	N/A	N/A
N6D45IS	43-7/8"	1	0.53	48.0	N/A	N/A	N/A	N/A
N6D45OS	51-1/16"	1	0.53	48.0	N/A	N/A	N/A	N/A
N6D90IS	70-7/8"	1	1.00	82.6	N/A	N/A	N/A	N/A
N6D90OS	78-7/8"	2	1.60	142.0	N/A	N/A	N/A	N/A

T-8 Lighting with Electronic Ballasts (120 Volt)

			Y LIGHTS* E ROW SHELF LIGHTS – PER ROW										MAXIMUM LIGHTING (6 ROWS)		
MODEL	CASE LENGTH	AMPS	WATTS	1	2	AMPS 3	4	5	1	2	WATTS 3	4	5	AMPS	WATTS
N6D30OS	39-5/8"	0.66	79.0	0.34	0.66	0.94	1.13	1.41	40.0	80.0	120.0	160.0	200.0	2.07	279.0
N6D45IS	43-7/8"	0.18	20.0	0.29	0.40	0.62	0.74	0.98	24.0	48.0	72.0	96.0	120.0	1.16	140.0
N6D45OS	51-1/16"	0.66	79.0	0.34	0.66	0.94	1.13	1.41	40.0	80.0	120.0	160.0	200.0	2.07	279.0
N6D90IS	70-7/8"	0.18	20.0	0.34	0.66	0.94	1.13	1.41	40.0	80.0	120.0	160.0	200.0	1.59	220.0
N6D90OS	78-7/8"	0.66	79.0	0.34	0.66	0.94	1.13	1.41	40.0	80.0	120.0	160.0	200.0	2.07	279.0

^{*} Standard lighting for this case is 1 row of canopy lights.

Defrost Data:

20.1001 2 4.44.													
					EPR SET	TINGS **		DEFROST WATER (LE					
DEFROST TYPE*	DEFROSTS PER DAY	DURATION TIME (MIN)	TERM.	USAGE	R22 (PSIG)	R404A (PSIG)	30OS	45IS	450S	90IS	90OS		
TIME OFF – ALL MODELS	4	24		MED TEMP	44	57	28.5	24.8	35.6	24.8	35.6		
ELECTRIC - ALL MODELS	4	24	41°F	MED TEMP	44	57	26.5	24.0	33.0	24.6	35.6		

^{*} If an Electronic Sensor is used for termination, it should be set at 70°F termination temperature. The sensor must be located in the

DEFROST CIRCUITS: OFF CYCLE defrost is standard (use TC defrost module) - **OPTIONAL ELECTRIC** defrost uses a single or 3 phase circuit.

CASE CIRCUITS: This case requires a 120V circuit for fans and lights.

ULSANITATION approved in accordance with ANSI/NSF - 7.

CASE BTUH REQUIREMENTS are calculated to produce approximately the indicated entering-air temperature with absolute maximum operating ambient limits of **75°F & 55RH**.

The information contained herein is based on technical analysis and/or tests performed in a controlled lab environment that are consistent with industry practices, and is intended as a reference for system sizing and configuration purposes only and for use by persons having technical skill at their own discretion and risk. Conditions of use are outside of Tyler's control and we do not assume and hereby disclaim any liability for results obtained or damages incurred through application of or reliance on the data presented, including but not limited to specific energy consumption with any particular model or installed application. SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE.

TYLER SPEC SHEET DWE – 1 DAIRY WEDGE

^{**} Evaporator temperature is based on the saturated pressure leaving the case.

^{***} Air velocity measured 1 hour after defrost at the top discharge air duct using an ALNOR JR. velometer with a scoop.

same location as the defrost termination klixon for that defrost type.


** Set EPR to give this pressure at the case




DAIRY WEDGE CROSS SECTIONS

N6DL45IS / N6DL90IS / N6DM90IS / N6DH45IS /N6DH90IS

N6DL30OS / N6DL45OS / N6DM45OS / N6DM90OS / N6DH45OS





DIMENSIONAL SPECIFICATION	N6DL45IS	N6DL30OS	N6DL45OS	N6DL90IS	N6DM45OS	N6DM90IS	N6DM90OS	N6DH45IS	N6DH45OS	N6DH90IS
А	79"	79"	79"	79"	79"	79"	79"	79"	79"	79"
В	39-3/4"	41"	39-3/4"	31-1/4"	39-3/4"	31-1/4"	30-5/8"	39-3/4"	39-3/4"	31-1/4"
С	59-1/4"	59-1/4"	59-1/4"	59-1/4"	59-1/4"	59-1/4"	59-1/4"	59-1/4"	59-1/4"	59-1/4"
D	30-5/8"	30-1/2"	28-5/8"	22-7/8"	28-5/8"	22-7/8"	20-9/16"	30-5/8"	28-5/8"	22-7/8"
E	56-3/4"	56-3/4"	56-3/4"	56-3/4"	52-7/8"	52-7/8"	52-7/8"	49-1/8"	49-1/8"	49-1/8"
F	18"	18"	18"	18"	21-3/4"	21-3/4"	21-3/4"	25-1/2"	25-1/2"	25-1/2"
G	9-1/8"	9-1/8"	9-1/8"	9-1/8"	9-1/8"	9-1/8"	9-1/8"	9-1/8"	9-1/8"	9-1/8"
Н	27-1/2"	27-1/2"	27-1/2"	20-3/4"	27-1/2"	20-3/4"	20-3/4"	27-1/2"	27-1/2"	20-3/4"
I	1-1/2"	1-1/2"	1-1/2"	1-1/2"	1-1/2"	1-1/2"	1-1/2"	1-1/2"	1-1/2"	1-1/2"
J	40-1/4"	41-9/16"	40-1/4"	31-7/16"	40-1/4"	31-7/16"	31-7/16"	40-1/4"	40-1/4"	31-7/16
K	4"	4"	4"	4"	4"	4"	4"	4"	4"	4"




DAIRY WEDGE FLOOR PLANS


N6DL30OS **N6DL45IS / N6DH45IS** 18" Rear of Case 43-7/8" -6-7/8 Rear of Case 27-13/16" 27-5/16" Base Legs Base 27-9/16" 18-1/16" 41-3/4" 28" Partition 27-3/4" 41-9/16" 27-1/2' 13-5/8" Overall Base 1-1/2" PVC Waste Outlet Case Depth 41-3/4" 39-7/8" Partition Overall Width 1-1/2" PVC Case Depth Waste Outlet 30.0° Electric > Front of Case NOTE: 5/8" Suction & 3/8" Liquid Refrigeration Lines NOTE: 5/8" Suction & 3/8" Liquid Refrigeration Lines 12"connect case-to-case. 39-5/8" connect case-to-case.

N6DL45OS / N6DM45OS / N6DH45OS

N6DL90IS / N6DM90IS / N6DH90IS



N6DM90OSNL



03-Jan-08